





REPUBLIC OF THE PHILIPPINES
DEPARTMENT OF AGRICULTURE
**BUREAU OF SOILS AND
WATER MANAGEMENT**
Elliptical Road Cor Visayas Ave., Diliman, Quezon City

**FERTILIZER GUIDE MAP
(Key Corn Areas)**

PROVINCE OF LEYTE



Projection : Transverse Mercator
Datum : PRRS 1992
DISCLAIMER : All political boundaries are not authoritative

LOCATION MAP



MISCELLANEOUS INFORMATION

SOURCES OF INFORMATION : Topographic information taken from NAMRIA Topographic Map at a scale of 1:50,000; Elevation data taken from SRTM 3 arc-second global dataset (2013); Bathymetry information taken from British Oceanographic Centre; Fertilizer guide data gathered through the Soil Health Assessment National Soil Sampling and Testing Project Phase II led by the Bureau of Soils and Water Management in partnership with the DA - Regional Field Office (RFO) and Local Government Units (LGUs).

Users noting errors or omissions in this publication are requested to inform the BSWM, SRDC Bldg., Elliptical Rd., cor Visayas Avenue, Diliman, Quezon City, Philippines or visit the BSWM website (<http://www.bswm.da.gov.ph>).

Copyright © 2018. All rights reserved to the Bureau of Soils and Water Management. No part of this publication may be reproduced, stored in a retrieval system or published without written consent from the BSWM.

Prepared and produced by the GEOMATICS AND SOIL INFORMATION TECHNOLOGY DIVISION, BSWM.

CONVENTIONAL SIGNS		
ROADS	BOUNDARY	HYDROLOGY
Expressway	Regional	Rivers / Lake
Trunk line	Provincial	Shoreline
Primary	District	PLACES
Secondary	City	Capital City / City
Tertiary	Municipal	Capital Town / Town
Residential		

Mapping Symbol	Description	All fertilizer recommendation options are recommended to apply additional 10-20 bags Organic Fertilizer per hectare														AREA			
		HYBRID CORN						OPEN-POLLINATED VARIETIES (OPV)											
		WET SEASON				Nutrient Requirement		Recommended Fertilizer Rate (bags/hectare)		WET SEASON				Nutrient Requirement		Recommended Fertilizer Rate (bags/hectare)		ha	%
		Recommended Fertilizer Rate (bags/hectare)								Recommended Fertilizer Rate (bags/hectare)									
		N	P ₂ O ₅	K ₂ O		N	P ₂ O ₅	K ₂ O		N	P ₂ O ₅	K ₂ O		N	P ₂ O ₅	K ₂ O			
1	L-L-L	120	60	60	"Complete" Option: (1st Application): 8.5 (14-14-14); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	60	60	"Complete" Option: (1-time Application): 8.5 (14-14-14); 2.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 2 (0-0-60);	80	60	60	"Complete" Option: (1st Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.75 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	60	"Complete" Option: (1-time Application): 8.5 (14-14-14); 1 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 2 (0-0-60);	37	0.25
2	L-L-ML	120	60	45	"Complete" Option: (1st Application): 6.5 (14-14-14); 0.75 (46-0-0); 1.75 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	60	45	"Complete" Option: (1-time Application): 6.5 (14-14-14); 3.25 (46-0-0); 1.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);	80	60	45	"Complete" Option: (1st Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	45	"Complete" Option: (1-time Application): 6.5 (14-14-14); 1.5 (46-0-0); 1.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);	24	0.16
3	L-L-MH	120	60	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1.5 (46-0-0); 3.5 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 4 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);	80	60	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 0.5 (46-0-0); 3.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 2.25 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);	231	1.54
4	L-L-H	120	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 2.5 (46-0-0); 6 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	80	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 6 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	787	5.25
5	L-ML-L	120	40	60	"Complete" Option: (1st Application): 5.75 (14-14-14); 1 (46-0-0); 0.75 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	40	60	"Complete" Option: (1-time Application): 5.75 (14-14-14); 3.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 2 (0-0-60);	80	40	60	"Complete" Option: (1st Application): 5.75 (14-14-14); 0.75 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	40	60	"Complete" Option: (1-time Application): 5.75 (14-14-14); 1.75 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 2 (0-0-60);	18	0.12
7	L-ML-MH	120	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1.5 (46-0-0); 1 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 4 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	80	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 0.5 (46-0-0); 1 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 2.25 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	62	0.42
8	L-ML-H	120	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	80	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	424	2.82
9	L-MH-L	120	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 1.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);	80	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);	41	0.27
10	L-MH-ML	120	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 1.75 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	80	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	149	0.99
11	L-MH-MH	120	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 1.75 (46-0-0); 0.5 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	80	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 0.5 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	234	1.56
12	L-MH-H	120	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 2.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	80	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	478	3.18
13	L-H-L	120	0	60	Single Element Option: (1st Application): 2.75 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	0	60	Single Element Option: (1-time Application): 5.25 (46-0-0); 2 (0-0-60);	80	7	60	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	7	60	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 3.25 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 0.75 (0-18-0); 2 (0-0-60);	197	1.31
14	L-H-ML	120	0	45	Single Element Option: (1st Application): 2.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	0	45	Single Element Option: (1-time Application): 5.25 (46-0-0); 1.5 (0-0-60);	80	7	45	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 3.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);	215	1.43
15	L-H-MH	120	0	30	Single Element Option: (1st Application): 2.75 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	0	30	Single Element Option: (1-time Application): 5.25 (46-0-0); 1 (0-0-60);	80	7	30	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 0.75 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	7	30	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 3.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);	491	3.27
16	L-H-H	120	0	7	Single Element Option: (1st Application): 2.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	0	7	Single Element Option: (1-time Application): 5.25 (46-0-0); 0.25 (0-0-60);	80	7	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	7	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 3.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60);	2,036	13.57
17	ML-L-L	100	60	60	"Complete" Option: (1st Application): 7.25 (14-14-14); 1 (0-18-0); 0.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 2 (0-0-60); (2nd Application): 2.25 (46														

LEGEND																			
Mapping Symbol	Description	All fertilizer recommendation options are recommended to apply additional 10-20 bags Organic Fertilizer per hectare												AREA					
		HYBRID CORN						OPEN-POLLINATED VARIETIES (OPV)											
		WET SEASON			DRY SEASON			WET SEASON			DRY SEASON			ha	%				
		Nutrient Requirement	Recommended Fertilizer Rate (bags/hectare)		Nutrient Requirement	Recommended Fertilizer Rate (bags/hectare)		Nutrient Requirement	Recommended Fertilizer Rate (bags/hectare)		Nutrient Requirement	Recommended Fertilizer Rate (bags/hectare)							
N-P-K	N	P ₂ O ₅	K ₂ O	N	P ₂ O ₅	K ₂ O	N	P ₂ O ₅	K ₂ O	N	P ₂ O ₅	K ₂ O	N	P ₂ O ₅	K ₂ O				
22	ML-ML-ML	100	40	45	"Complete" Option: (1st Application): 5.75 (14-14-14); 0.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 2.75 (46-0-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);	60	40	45	"Complete" Option: (1st Application): 4.25 (14-14-14); 1 (0-18-0); 0.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.5 (0-0-60); (2nd Application): 1.25(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 1 (46-0-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);	197	1.31
23	ML-ML-MH	100	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1 (46-0-0); 1 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 3 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	60	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1 (0-0-60); (2nd Application): 1.25(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1.5 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	325	2.17
24	ML-ML-H	100	40	7	"Complete" Option: (1st Application): 4.25 (14-14-14); 2 (46-0-0); 3.75 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 4 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	60	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.25(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	555	3.7
25	ML-MH-L	100	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);	60	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);	197	1.31
26	ML-MH-ML	100	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	60	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	367	2.45
27	ML-MH-MH	100	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 0.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	60	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 0.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 1.5(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	250	1.67
28	ML-MH-H	100	20	7	"Complete" Option: (1st Application): 3 (14-14-14); 2 (46-0-0); 1.5 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 4 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	60	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.5(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	614	4.09
29	ML-H-L	100	0	60	Single Element Option: (1st Application): 2.25 (46-0-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	0	60	Single Element Option: (1-time Application): 4.5 (46-0-0); 2 (0-0-60);	60	7	60	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 1.75 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1 (46-0-0); 2 (0-0-60); (2nd Application): 1.5(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	7	60	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 2 (0-0-60);	374	2.49
30	ML-H-ML	100	0	45	Single Element Option: (1st Application): 2.25 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	0	45	Single Element Option: (1-time Application): 4.5 (46-0-0); 1.5 (0-0-60);	60	7	45	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 1.25 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);	427	2.84
31	ML-H-MH	100	0	30	Single Element Option: (1st Application): 2.25 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	0	30	Single Element Option: (1-time Application): 4.5 (46-0-0); 1 (0-0-60);	60	7	30	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 0.75 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.5(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	7	30	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);	529	3.53
32	ML-H-H	100	0	7	Single Element Option: (1st Application): 2.25 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);	100	0	7	Single Element Option: (1-time Application): 4.5 (46-0-0); 0.25 (0-0-60);	60	7	7	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.5(46-0-0) Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	7	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60);	718	4.79
33	MH-L-L	80	60	60	"Complete" Option: (1st Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.75 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	60	"Complete" Option: (1-time Application): 8.5 (14-14-14); 1 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 2 (0-0-60);	40	60	60	"Complete" Option: (1st Application): 3 (14-14-14); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 2 (0-0-60); (2nd Application): 0(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 6.75 (0-18-0); 2 (0-0-60); (2nd Application): 1 (46-0-0);	40	60	60	"Complete" Option: (1-time Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 2 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 6.75 (0-18-0); 2 (0-0-60);	122	0.82
34	MH-L-ML	80	60	45	"Complete" Option: (1st Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	45	"Complete" Option: (1-time Application): 6.5 (14-14-14); 1.5 (46-0-0); 1.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);	40	60	45	"Complete" Option: (1st Application): 3 (14-14-14); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1.5 (0-0-60); (2nd Application): 0(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1 (46-0-0);	40	60	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);	41	0.27
35	MH-L-MH	80	60	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 0.5 (46-0-0); 3.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 2.25 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);	40	60	30	"Complete" Option: (1st Application): 3 (14-14-14); 4.5 (0-18-0); 0.5 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1 (0-0-60); (2nd Application): 0(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 1 (46-0-0);	40	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 0.5 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);	28	0.19
36	MH-L-H	80	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 6 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	40	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0); 6 (0-18-0); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 0(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1 (46-0-0);	40	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	337	2.25
37	MH-ML-L	80	40	60	"Complete" Option: (1st Application): 5.75 (14-14-14); 0.75 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st														

Mapping Symbol	Description	All fertilizer recommendation options are recommended to apply additional 10-20 bags Organic Fertilizer per hectare														AREA			
		HYBRID CORN									OPEN-POLLINATED VARIETIES (OPV)								
		WET SEASON				DRY SEASON					WET SEASON				DRY SEASON				
		Nutrient Requirement			Recommended Fertilizer Rate (bags/hectare)	Nutrient Requirement			Recommended Fertilizer Rate (bags/hectare)	Nutrient Requirement			Recommended Fertilizer Rate (bags/hectare)	Nutrient Requirement			Recommended Fertilizer Rate (bags/hectare)	ha	%
N	P ₂ O ₅	K ₂ O	N	P ₂ O ₅		K ₂ O	N	P ₂ O ₅		K ₂ O	N	P ₂ O ₅		K ₂ O					
43	MH-MH-MH	80	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 0.5 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	40	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.25 (46-0-0); 1 (0-0-60); (2nd Application): 1(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 1 (46-0-0);	40	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 1 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 1 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	66	0.44
44	MH-MH-H	80	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	40	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.25 (46-0-0); 0.25 (0-0-60); (2nd Application): 1(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1 (46-0-0);	40	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 1 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	407	2.71
45	MH-H-L	80	0	60	Single Element Option: (1st Application): 1.75 (46-0-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	0	60	Single Element Option: (1-time Application): 3.5 (46-0-0); 2 (0-0-60);	40	7	60	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0); 1.75 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.75 (46-0-0); 2 (0-0-60); (2nd Application): 1(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 0.75 (0-18-0); 2 (0-0-60); (2nd Application): 1 (46-0-0);	40	7	60	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 1.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 0.75 (0-18-0); 2 (0-0-60);	28	0.19
46	MH-H-ML	80	0	45	Single Element Option: (1st Application): 1.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	0	45	Single Element Option: (1-time Application): 3.5 (46-0-0); 1.5 (0-0-60);	40	7	45	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0); 1.25 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1 (46-0-0);	40	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);	116	0.77
47	MH-H-MH	80	0	30	Single Element Option: (1st Application): 1.75 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	0	30	Single Element Option: (1-time Application): 3.5 (46-0-0); 1 (0-0-60);	40	7	30	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0); 0.75 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 1(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 1 (46-0-0);	40	7	30	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);	29	0.19
48	MH-H-H	80	0	7	Single Element Option: (1st Application): 1.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	0	7	Single Element Option: (1-time Application): 3.5 (46-0-0); 0.25 (0-0-60);	40	7	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0);	40	7	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60);	452	3.01
50	H-L-ML	60	60	45	"Complete" Option: (1st Application): 4.25 (14-14-14); 3.5 (0-18-0); 0.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1.5 (0-0-60); (2nd Application): 0.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	60	45	"Complete" Option: (1-time Application): 6.5 (14-14-14); 0.75 (46-0-0); 1.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);	20	60	45	"Complete" Option: (1st Application): 1.5 (14-14-14); 5.5 (0-18-0); 1.25 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1.5 (0-0-60); (2nd Application): -1(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	60	45	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (0-18-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); -1 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);	24	0.16
52	H-L-H	60	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 6 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	20	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 6 (0-18-0); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): -1(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); -1 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	73	0.49
55	H-ML-MH	60	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1 (0-0-60); (2nd Application): 1.25 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1.5 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	20	40	30	"Complete" Option: (1st Application): 1.5 (14-14-14); 3.5 (0-18-0); 0.75 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1 (0-0-60); (2nd Application): 0(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	40	30	"Complete" Option: (1-time Application): 3 (14-14-14); 2.25 (0-18-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	33	0.22
56	H-ML-H	60	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.25 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	20	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 3.75 (0-18-0); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 0(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	198	1.32
57	H-MH-L	60	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);	20	20	60	"Complete" Option: (1st Application): 1.5 (14-14-14); 1 (0-18-0); 1.75 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (0-0-60); (2nd Application): 0.25(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 0.25 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);	29	0.19
58	H-MH-ML	60	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	20	20	45	"Complete" Option: (1st Application): 1.5 (14-14-14); 1 (0-18-0); 1.25 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (0-0-60); (2nd Application): 0.25(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 0.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	48	0.32
59	H-MH-MH	60	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 0.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	20	20	30	"Complete" Option: (1st Application): 1.5 (14-14-14); 1 (0-18-0); 0.75 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (0-0-60); (2nd Application): 0.25(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 0.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	60	0.4
60	H-MH-H	60	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	20	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 1.5 (0-18-0); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.25 (0-0-60); (2nd Application): 0.25(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 0.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	138	0.92
62	H-H-ML	60	0	45	Single Element Option: (1st Application): 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	0	45	Single Element Option: (1-time Application): 2.75 (46-0-0); 1.5 (0-0-60);	20	7	45	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 1.25 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.25 (46-0-0); 1.5 (0-0-60); (2nd Application): 0.5(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);	87	0.58
63	H-H-MH	60	0	30	Single Element Option: (1st Application): 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	0	30	Single Element Option: (1-time Application): 2.75 (46-0-0); 1 (0-0-60);	20	7	30	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 0.75 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.25 (46-0-0); 1 (0-0-60); (2nd Application): 0.5(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	7	30	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);	23	0.15
64	H-H-H	60	0	7	Single Element Option: (1st Application): 1.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	0	7	Single Element Option: (1-time Application): 2.75 (46-0-0); 0.25 (0-0-60);	20	7	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.25 (46-0-0); 0.2						

Mode of Application of Fertilizer

Wet Season

First Application: Apply all the recommended phosphate and potash and 1/2 of Nitrogen fertilizer in a band about 2 inches to the sides of and about 2 inches below the seed during planting.

Second Application: Side-dress the remaining 1/2 Nitrogen fertilizer when the plants are about four (4) weeks old or when the plants are knee high (12-19 inches high). Hilling up is recommended after the application of the fertilizer for better growth development.

Dry Season

Apply all the recommended fertilizers at planting or three (3) weeks after planting. Hilling up is recommended after the application of the fertilizer for better growth development