




LEGEND			All fertilizer recommendation options are recommended to apply additional 10-20 bags Organic Fertilizer per hectare																				AREA		
Mapping Symbol	Description	HYBRID CORN												OPEN-POLLINATED VARIETIES (OPV)											
		WET SEASON						DRY SEASON						WET SEASON				DRY SEASON							
		Nutrient N P ₂ O ₅ K ₂ O			Recommended Fertilizer Rate (bags/hectare)			Nutrient N P ₂ O ₅ K ₂ O			Recommended Fertilizer Rate (bags/hectare)			Nutrient N P ₂ O ₅ K ₂ O		Recommended Fertilizer Rate (bags/hectare)		Nutrient N P ₂ O ₅ K ₂ O		Recommended Fertilizer Rate (bags/hectare)		ha			%
1	L-L-L	120	60	60	"Complete" Option: (1st Application): 8.5 (14-14-14); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	60	60	"Complete" Option: (1-time Application): 8.5 (14-14-14); 2.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 2 (0-0-60);			80	60	60	"Complete" Option: (1st Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.75 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	60	60	"Complete" Option: (1-time Application): 8.5 (14-14-14); 1 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 2 (0-0-60);		248	1.26
2	L-L-ML	120	60	45	"Complete" Option: (1st Application): 6.5 (14-14-14); 0.75 (46-0-0); 1.75 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	60	45	"Complete" Option: (1-time Application): 6.5 (14-14-14); 3.25 (46-0-0); 1.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);			80	60	45	"Complete" Option: (1st Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	60	45	"Complete" Option: (1-time Application): 6.5 (14-14-14); 1.5 (46-0-0); 1.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);		1,264	6.43
3	L-L-MH	120	60	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1.5 (46-0-0); 3.5 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 4 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);			80	60	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 0.5 (46-0-0); 3.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 2.25 (46-0-0); 3.5 (0-18-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);		1,752	8.91
4	L-L-H	120	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 2.5 (46-0-0); 6 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);			80	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 6 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);		1,408	7.16
6	L-ML-ML	120	40	45	"Complete" Option: (1st Application): 5.75 (14-14-14); 1 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 3.5 (46-0-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);			80	40	45	"Complete" Option: (1st Application): 5.75 (14-14-14); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 1.75 (46-0-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);		358	1.82
7	L-ML-MH	120	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1.5 (46-0-0); 1 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 4 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);			80	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 0.5 (46-0-0); 1 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 2.25 (46-0-0); 1 (0-18-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);		473	2.40
8	L-ML-H	120	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);			80	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 3.75 (0-18-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);		1,209	6.15
9	L-MH-L	120	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 1.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);			80	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);		132	0.67
10	L-MH-ML	120	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 1.75 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);			80	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);		674	3.43
11	L-MH-MH	120	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 1.75 (46-0-0); 0.5 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);			80	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 0.5 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);		776	3.94
12	L-MH-H	120	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 2.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);			80	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.5 (0-18-0-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);		800	4.07
14	L-H-ML	120	0	45	Single Element Option: (1st Application): 2.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	0	45	Single Element Option: (1-time Application): 5.25 (46-0-0); 1.5 (0-0-60);			80	7	45	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.25 (0-0-60-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 3.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);		251	1.28
15	L-H-MH	120	0	30	Single Element Option: (1st Application): 2.75 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	0	30	Single Element Option: (1-time Application): 5.25 (46-0-0); 1 (0-0-60);			80	7	30	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 0.75 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	7	30	"Complete" Option: (1-time Application): 0.75 (16-20-0); 3.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);		614	3.12
16	L-H-H	120	0	7	Single Element Option: (1st Application): 2.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);			120	0	7	Single Element Option: (1-time Application): 5.25 (46-0-0); 0.25 (0-0-60);			80	7	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0) Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);		80	7	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 3.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60);		1,860	9.46
18	ML-L-ML	100	60	45	"Complete" Option: (1st Application): 6.5 (14-14-14); 0.25 (46-0-0); 1.75 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	60	45	"Complete" Option: (1-time Application): 6.5 (14-14-14); 2.5 (46-0-0); 1.75 (0-18-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 2.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);			60	60	45	"Complete" Option: (1st Application): 4.25 (14-14-14); 3.5 (0-18-0); 0.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1.5 (0-0-60								

All fertilizer recommendation options are recommended to apply additional 10-20 bags Organic Fertilizer per hectare																	AREA											
Mapping Symbol	Description	HYBRID CORN												OPEN-POLLINATED VARIETIES (OPV)														
		WET SEASON						DRY SEASON						WET SEASON						DRY SEASON								
		Nutrient N P ₂ O ₅ K ₂ O			Recommended Fertilizer Rate (bags/hectare)			Nutrient N P ₂ O ₅ K ₂ O			Recommended Fertilizer Rate (bags/hectare)			Nutrient N P ₂ O ₅ K ₂ O					Recommended Fertilizer Rate (bags/hectare)			Nutrient N P ₂ O ₅ K ₂ O			Recommended Fertilizer Rate (bags/hectare)			ha
20	ML-L-H	100	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2 (46-0-0); 6 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.25 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 4 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 2.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);			60	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1 (46-0-0); 6 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);			692	3.52	
22	ML-ML-ML	100	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 0.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1-time Application): 2.25 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 2.75 (46-0-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);			60	40	45	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1 (0-18-0); 0.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.5 (0-0-60); (2nd Application): 1.25 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	40	45	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1 (46-0-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);			10	0.05	
23	ML-ML-MH	100	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1 (46-0-0); 1 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1-time Application): 2.25 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 3 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);			60	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1 (0-0-60); (2nd Application): 1.25 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1.5 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);			350	1.78	
24	ML-ML-H	100	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2 (46-0-0); 3.75 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1-time Application): 2.25 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 4 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);			60	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.25 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);			469	2.38	
26	ML-MH-ML	100	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1-time Application): 2.25 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	20	45	c	"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);			60	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);			269	1.37
27	ML-MH-MH	100	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 1.5 (46-0-0); 0.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1-time Application): 2.25 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);			60	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 0.5 (46-0-0); 0.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);			367	1.87	
28	ML-MH-H	100	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2 (46-0-0); 1.5 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1-time Application): 2.25 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 4 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);			60	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);			365	1.86	
30	ML-H-ML	100	0	45	Single Element Option: (1-time Application): 2.25 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	0	45	Single Element Option: (1-time Application): 4.5 (46-0-0); 1.5 (0-0-60);			60	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 1 (46-0-0); 1.25 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);			149	0.76	
31	ML-H-MH	100	0	30	Single Element Option: (1-time Application): 2.25 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	0	30	Single Element Option: (1-time Application): 4.5 (46-0-0); 1 (0-0-60);			60	7	30	"Complete" Option: (1-time Application): 1 (14-14-14); 1 (46-0-0); 0.75 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	7	30	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);			521	2.65	
32	ML-H-H	100	0	7	Single Element Option: (1-time Application): 2.25 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);			100	0	7	Single Element Option: (1-time Application): 4.5 (46-0-0); 0.25 (0-0-60);			60	7	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1 (46-0-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0) Single Element Option: (1-time Application): 1.5 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);			60	7	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60);			1,145	5.82	
35	MH-L-MH	80	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 0.5 (46-0-0); 3.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1-time Application): 1.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);			80	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 2.25 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);			40	60	30	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (0-18-0); 0.5 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1 (0-0-60); (2nd Application): 0.46-0-0 Single Element Option: (1-time Application): 1 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 1 (46-0-0);			40	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 0.5 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);			177	0.90	
36	MH-L-H	80	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 6 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1-time Application): 1.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);			80	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);			40	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1 (46-0-0); 1.25 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 0.46-0-0 Single Element Option: (1-time Application): 1 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1 (46-0-0);			40	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);			397	2.02	
38	MH-ML-ML	80	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1-time Application): 1.75 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);			80	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 1.75 (46-0-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);			40	40	45	"Complete" Option: (1-time Application): 3 (14-14-14); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.5 (0-0-60); (2nd Application): 0.5 (46-0-0) Single Element Option: (1-time Application): 1 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 1 (46-0-0);			40	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);			8	0.04	
39	MH-ML-MH	80	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 0.5 (46-0-0); 1 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1-time Application): 1.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);			80	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 2.25 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);			40	40	30	"Complete" Option: (1-time Application): 3 (14-14-14); 2.25 (0-18-0); 0.5 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1 (0-0-60); (2nd Application): 0.5 (46-0-0) Single Element Option: (1-time Application): 1 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1 (46-0-0);			40	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 0.5 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);			94	0.48	
40	MH-ML-H	80	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1-time Application): 1.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);			80	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);			40	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 3.75 (0-18-0); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0) Single Element Option: (1-time Application): 1 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1 (46-0-0);			40	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 3.75 (0-18-0); "Ammo					

LEGEND																			
Mapping Symbol	Description	All fertilizer recommendation options are recommended to apply additional 10-20 bags Organic Fertilizer per hectare														AREA			
		HYBRID CORN							OPEN-POLLINATED VARIETIES (OPV)										
		WET SEASON				DRY SEASON			WET SEASON				DRY SEASON						
		Nutrient			Recommended Fertilizer Rate (bags/hectare)	Nutrient			Recommended Fertilizer Rate (bags/hectare)	Nutrient			Recommended Fertilizer Rate (bags/hectare)	Nutrient			Recommended Fertilizer Rate (bags/hectare)		
N-P-K	N	P ₂ O ₅ K ₂ O	N	P ₂ O ₅ K ₂ O		N	P ₂ O ₅ K ₂ O	N		P ₂ O ₅ K ₂ O									
44	MH-MH-H	80	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	40	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.25 (46-0-0); 0.25 (0-0-60); (2nd Application): 1(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1 (46-0-0);	40	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 1 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	81	0.41
46	MH-H-ML	80	0	45	Single Element Option: (1st Application): 1.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	0	45	Single Element Option: (1-time Application): 3.5 (46-0-0); 1.5 (0-0-60);	40	7	45	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0); 1.25 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1 (46-0-0);	40	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);	107	0.54
47	MH-H-MH	80	0	30	Single Element Option: (1st Application): 1.75 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	0	30	Single Element Option: (1-time Application): 3.5 (46-0-0); 1 (0-0-60);	40	7	30	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0); 0.75 (0-0-60); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 1(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 1 (46-0-0);	40	7	30	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);	347	1.76
48	MH-H-H	80	0	7	Single Element Option: (1st Application): 1.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	0	7	Single Element Option: (1-time Application): 3.5 (46-0-0); 0.25 (0-0-60);	40	7	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.5 (46-0-0); (2nd Application): 1 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 1(46-0-0) Single Element Option: (1st Application): 1 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1 (46-0-0);	40	7	7	"Complete" Option: (1-time Application): 1 (14-14-14); 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1.75 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60);	541	2.75
51	H-L-MH	60	60	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 3.5 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1 (0-0-60); (2nd Application): 0.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1.5 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);	20	60	30	"Complete" Option: (1st Application): 1.5 (14-14-14); 5.5 (0-18-0); 0.75 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1 (0-0-60); (2nd Application): -1(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	60	30	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (0-18-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); -1 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);	19	0.10
52	H-L-H	60	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 6 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	20	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 6 (0-18-0); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): -1(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); -1 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	310	1.58
55	H-ML-MH	60	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1 (0-0-60); (2nd Application): 1.25 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1.5 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	20	40	30	"Complete" Option: (1st Application): 1.5 (14-14-14); 3.5 (0-18-0); 0.75 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1 (0-0-60); (2nd Application): 0(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	40	30	"Complete" Option: (1-time Application): 3 (14-14-14); 2.25 (0-18-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	8	0.04
56	H-ML-H	60	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.25 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	20	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 3.75 (0-18-0); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 0(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	73	0.37
58	H-MH-ML	60	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	20	20	45	"Complete" Option: (1st Application): 1.5 (14-14-14); 1 (0-18-0); 1.25 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (0-0-60); (2nd Application): 0.25(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 0.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	19	0.10
60	H-MH-H	60	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	20	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 1.5 (0-18-0); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.25 (0-0-60); (2nd Application): 0.25(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 0.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	21	0.11
62	H-H-ML	60	0	45	Single Element Option: (1st Application): 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	0	45	Single Element Option: (1-time Application): 2.75 (46-0-0); 1.5 (0-0-60);	20	7	45	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 1.25 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.25 (46-0-0); 1.5 (0-0-60); (2nd Application): 0.5(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);	17	0.09
	H-H-MH	60	0	30	Single Element Option: (1st Application): 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	0	30	Single Element Option: (1-time Application): 2.75 (46-0-0); 1 (0-0-60);	20	7	30	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); 0.75 (0-0-60); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.25 (46-0-0); 1 (0-0-60); (2nd Application): 0.5(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	7	30	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);	112	0.57
64	H-H-H	60	0	7	Single Element Option: (1st Application): 1.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);	60	0	7	Single Element Option: (1-time Application): 2.75 (46-0-0); 0.25 (0-0-60);	20	7	7	"Complete" Option: (1st Application): 1 (14-14-14); 0.25 (46-0-0); (2nd Application): 0.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 0.25 (46-0-0); 0.25 (0-0-60); (2nd Application): 0.5(46-0-0) Single Element Option: (1st Application): 0.5 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 0.5 (46-0-0);	20	7	7	"Complete" Option: (1-time Application): 1 (14-14-14); 0.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 1 (46-0-0); 0.75 (0-18-0); 0.25 (0-0-60);	272	1.38
																	TOTAL	19,671	100.00

Mode of Application of Fertilizer
Wet Season
First Application: Apply all the recommended phosphate and potash and 1/2 of Nitrogen fertilizer in a band about 2 inches to the sides of and about 2 inches below the seed during planting.
Second Application: Side-dress the remaining 1/2 Nitrogen fertilizer when the plants are about four (4) weeks old or when the plants are knee high (12-19 inches high). Hilling up is recommended after the application of the fertilizer for better growth development.
Dry Season
Apply all the recommended fertilizers at planting or three (3) weeks after planting. Hilling up is recommended after the application of the fertilizer for better growth development